

**Specification**

**Spy CCD Camera**

SPY CCD CAMERA	
Item NO.	HS-C1xx
Video system.	NTSC/PAL
Number of Effective Pixels	510X492(NTSC)
	500X582(PAL)
CCD Image Sensor	1/4" Interline CCD
Scanning System	2:1 INTERLACE
Synchronization	INTERNAL
Resolution (TV Lines)	350 TV LINE
S/N Ratio	more than 48dB
Minimum Illumination	0.2 Lux / F 1.4
Electronic Shutter	1/50 - 1/120,000
Horizontal Sync Frequency	NTSC(EIA)-15.73kHz / PAL(CCIR)-15.62kHz
Vertical Sync Frequency	NTSC(EIA)-60kHz / PAL(CCIR)-50kHz
Gamma Consumption	0.45
Video Output	1Vp-p , 75ohms Composite
Audio Output	Frequency 20-16000Hz,S/N ratio more than 63dB SPL(at 1000Hz)(Ordering in advance)
Audio Standard	Frequency 20-16000Hz,S/N ratio more than 58dB
Built-In Lens	4.3mm/F2.0
Storage Temperature	-30 to 60 Degree C
Working Temperature	-10 to 45 Degree C
Power Source	DC 9-12V(standard)
Power Current	70mA(max)
Dimension (mm)	23mmX27mm



HS-C120



HS-C121



HS-C122



HS-C123



HS-C124



HS-C131

**Other mode**



MSX-2400B



MSR-A2410B



TXT-BOX

**Receiver**


MODEL	MRX-2400B	MRX-1200B	MRX-0900B
Channel Frequency	2413, 2432, 2451, 2470	1080, 1120, 1160, 1200	910, 980, 1010, 1040
Video Input	1 Vp-p Composite Video		
Audio Input	2 Vp-p (max)		
Audio Sub Carrier	5.5MHz		
Operating Voltage	DC 5 V		
Power Current	360mA		
Batter Charge Time	2.5Hrs		
Operating Temperature	10-40 Degree C		
Operating Humidity	20-80%		
Dimensions	110mmx67mmx21.5mm		
Weight	117g		

MODEL	MSR-A2410B	MSR-B1210B	MSR-C0910B
Channel Frequency	2413, 2432, 2451, 2470	1080, 1120, 1160, 1200	910, 980, 1010, 1040
Video Input	1 Vp-p Composite Video		
Audio Input	2 Vp-p (max)		
Audio Sub Carrier	5.5MHz		
Operating Voltage	DC 12 V		
Power Current	380mA		
Batter Charge Time	2.5Hrs		
Operating Temperature	10-40 Degree C		
Operating Humidity	20-80%		
Dimensions	21mmx80mmx125mm		
Weight	165g		

**Transmitter**

MODEL	TXT-AB2	TXT-AB6	TXT-BB1	TXT-BB5
Channel Frequency	2413,2432,2451,2470 (MHz)		1080,1120,1160,1200 (MHz)	
Frequency Deviation	200kHz			
RF Output Power	200mW	600mW	100mW	500mW
Video Input	1 Vp-p75 ohms Composite			
Audio Input	2 Vp-p (max)			
Audio Sub Carrier	5.5MHz			
Charge Voltage	DC 9 V			
Charge Current	800mA			
Output Voltage	DC 12V			
Output Current	400mA(max)			
Capacity	900mAh(DC 9V)			
Operating Temperature	10-40 Degree C			
Operating Humidity	20-80%			
Dimension (mm)	55x70x15	55x86x20	55x70x15	55x86x20

**KIT**



HFS-T121T-A2



BB62124