

Specification


HIDDEN CCD Camera

CCD HIDDEN CAMERA					
Item NO.		MS- <u>C</u> _B 365	MS- <u>C</u> _B 665	MS- <u>C</u> _B 465	MS- <u>C</u> _B 865
Video system.		NTSC/PAL (Color) & EIA/CCIR (BW)			
CCD Image Sensor		1/3" Interline CCD		1/4" Interline CCD	
Number of Effective Pixels	PAL(CCIR)	500x528	752x582	500x528	752x582
	NTSC(EIA)	510x492	768x494	510x492	768x494
Scanning System		2:1 INTERLACE			
Synchronization		INTERNAL			
S/N Ratio		more than 48dB			
Dimensions(mm)		67x85x46 mm			
Resolution (TV Lines)	COLOR	380	470	350	470
	B/W	420	570	420	570
Minimum Illumination		0.2Lux / F 1.2 (color) & 0.02Lux / F 1.2 (BW)			
Electronic Shutter		1/50 - 1/120,000			
Built-Lens		3.6mm/F2.0			
Lens Angle		3.6mm/92 Degree		3.6mm/70 Degree	
Horizontal Sync Frequency		NTSC(EIA)-15.734kHz / PAL(CCIR)-15.625kHz			
Vertical Sync Frequency		NTSC(EIA)-60Hz / PAL(CCIR)-50Hz			
Gamma Consumption		0.45			
Video Output		1Vp-p , 75ohms Composite			
Audio Output		Frequency 20-16000Hz,S/N ratio more than 58dB (Optional)			
Storage Temperature		-30 to 60 Degree C			
Working Temperature		-10 to 45 Degree C			
Power Source		DC 12V(standard)			
Power Current		120mA(max)			
Weight		90g			



MS-C_Bx65x

Dimensions



Ordering Information

MODEL	MICRO	MIC	NOTE
MS-C365	3.6mm / F2.0		1/3" CCD M.RES
MS-C665	3.6mm / F2.0		1/3" CCD H.RES
MS-C465	3.6mm / F2.0		1/4" CCD M.RES
MS-C865	3.6mm / F2.0		1/4" CCD H.RES
MS-C365A	3.6mm / F2.0	●	1/3" CCD M.RES
MS-C665A	3.6mm / F2.0	●	1/3" CCD H.RES
MS-C465A	3.6mm / F2.0	●	1/4" CCD M.RES
MS-C865A	3.6mm / F2.0	●	1/4" CCD H.RES
MS-B365	3.6mm / F2.0		1/3" CCD M.RES
MS-B665	3.6mm / F2.0		1/3" CCD H.RES
MS-B465	3.6mm / F2.0		1/4" CCD M.RES
MS-B865	3.6mm / F2.0		1/4" CCD H.RES
MS-B365A	3.6mm / F2.0	●	1/3" CCD M.RES
MS-B665A	3.6mm / F2.0	●	1/3" CCD H.RES
MS-B465A	3.6mm / F2.0	●	1/4" CCD M.RES
MS-B865A	3.6mm / F2.0	●	1/4" CCD H.RES

NOTE:

1/4" CCD **M.RES.** : **M**: Medium resolution ; **H**: High resolution
 MS-x365 : **C**: Color ; **B**: BW
 MS-x365**G** : **G**: Micro lens ; **P**: Pin Hole
 MS-x365**A** : **A**: W/Microphone

Instruction Drawing

