

Specifications:

Display	2.4" TFT (480x234 pixels)
External Memory	SD Card memory slot (support SDHC, 8G)
Resolution	VGA, 30fps real time recording
Compression	MPEG-4 format
Video	Synchronized audio & video recording/ playback
Function	Date Time stamp function Power saving Low power alert LCD display on/ off Schedule recording Overwrite function Standby
PC Interface	USB2.0
Microphone	External with camera (optional)
Speaker	Built-in
Connector	USB & DC-in jack
TV out/ in jack	
Video Output	NTSC/ PAL auto-detection
O/S	Windows 2000/ XP/ Vista
Power	Built-in rechargeable Li-ion battery (3.7V/ 1070mA)
Dimension	66.2 (L) x 95.5 (H) x 18.5 (W) mm
Specifications are subject to change without prior notice.	



Date and Time

use 5 D Key the <- or -> to select an item and the UP or DOWN to change its value, push down to Enter

Schedule Record

3 level of selectable schedule recording timer from 1 minutes to 240 minutes(4hrs)

Overwrite

settings REC MODE
continuous (REC continuous to SD Data Storage Full)
overwrite (REC loop duration that continuously overwrite records to SD Data Storage)

Standy

settings Power saving start timer 2, 5, 10 min.

use 5 D Key UP or DOWN to select an item , push down to Enter

Stamp

SD Card Capacity	Recording Time
512 MB	26 min
1G	52 min
2G	1 hr 44 min
4G	3 hr 28 min

