



unit:(±0.5mm)

Features:
supply DC Power 9V (DC 5V optional with UCD-110-5V) output for Camera and AV composite input
Captures video at resolutions up to 720 x 480 (NTSC) or 720 x 576 (PAL/SECAM)
Connects to Windows XP machines USB 2.0 port
Integrated input connections with mini 4 pin
Video can be directly captured as .AVI, compressed AVI, MPEG-1 or Windows Media Video
Capture VIDEO from any SPY Camera to your computer hard drive
Burn Video to disc in Video CD format
CD Driver step :
Insert the CD into your PC CD-ROM drive.
RUN PC CD-ROM drive: SETUP.EXE
Connect the UCD-100 to an available USB 2.0 Port.
Follow driver installation steps to complete hardware driver installation.
PC Requirements:
Windows XP (Windows 98 or higher)
CPU Speed of 2.0 GHz or faster
256 MB of RAM (512 recommended)
600 MB of hard drive space for software installation
4 GB+ of hard disk for video capture space
Available USB 2.0 port
Graphic card set to 1024 x 768
Sound Card for audio playback
CD drive for software installation
Power Supply:(Ordering in advance)
DC Power 5V (UCD-110-5V)
DC Power 9V (UCD-110-9V)
DC Power 12V (UCD-110-12V)



UCD-110

Instruction Drawing & Description

