



Feature

- High Sensitivity!
- MINI MICROPHONE
- Dimension :26.4x 9.2 mm
- Compact size



MS-3500



MS-3200-01

Specification

unit : mm (±0.2)

Model	MS-3500	MS-3200-01
Frequency	20-16000Hz	
S/N Ratio	More than 58dB	
Impedance	150 ohm +/- 20% (at 1000Hz)	
Sensitivity	-44-dB+/-3dB(at 1000Hz)	
Power Source	DC 12V	
S/N Ratio	20mA(max)	
Dimension	6 x 18 x 4 mm	
weight	5g (without cable)	
Note	Condenser Microphone	
	Less gain value changeable type	

Other information

MS-6200

- with 3M double-sided tape easy installation

Frequency: 20 -16000Hz
S/N Ratio: more than 58dB
Impedance: 600 ohm +/- 20% (at 1000Hz)
Dimension : 26.4 x 9.2 mm



MS-6300W

- MINI MICROPHONE

Frequency: 20 -16000Hz
S/N Ratio: more than 58dB
Impedance: 150 ohms ±20%(at 1000 HZ)
Power : DC 7~12V
Dimensions: 6x18x3.5 mm

