



UNIT: ± 0.5 mm



Specification

Model	8M292221R-M6
Image circle	$\phi 4.95$ mm
Focal length	2.92 mm
Aperture F/no	$2.2 \pm 5\%$
F.O.V (D)	76.8°
FBFL	0.65 ± 0.1 mm
TTL	3.6 ± 0.15 mm
TV DIST	$< 1.5\%$
Barrel Material	PC
Thread	$M6 \times P0.25$
Lens construction	4P