



UNIT: ± 0.5 mm

Specification

Model	L1428IR-M7
Image circle	5.0mm
Focal length	1.4 mm
Aperture F/no	2.8 $\pm 5\%$
F.O.V (D/H/V)	154.3° / 126° / 93°
Flange Back length	3REF.1.29 $\pm 0.3\%$
IR-CUT Coating Filter	650nm
Track In Total	11.49 $\pm 5\%$
MTF	801p/mm(0.8 field) > 30%
Thread	M7 x P0.5
Lens construction	5 Elements