



Specification

Model	L1653		
Coverage area	1/2"	1/3"	1/4"
H/V/D FOV	27.4 / 22.1 / 12.6	16.8 / 12.6 / 21.0	16.2 / 9.5 / 15.8
Effective Focal Length (mm)	16.0		
Working F no.	5.3		
Distortion (%)	-0.15%@1.3"		
Back Focal Length (mm)	12.3		
Flange Back Focal Length (mm)	8.9		
Track In Total (mm)	23.35		
Thread	M12*P0.5		
Retaining Ring (Ø)	14		
Lens Construction	3		
Filter	N/A		