



UNIT: ±0.5mm

Specification

Model	L22820IR-M7
Image circle	4.8mm
Focal length	2.28 mm ±5%
Back Focal length	3.0mm ±5%
Aperture F/no	2.0 ±5%
F.O.V (D/H/V)	139.3° / 98.5° / 70.5°
Flange Back length	2.92mm ±5%(In AIR)
IR-CUT Coating Filter	650nm
IRIS	Fixed
MTF	801p/mm(0.8 field)>30%
Mount	M7 x P0.5
Lens construction	5G + IRF(6E)