



UNIT:±0.5mm

Feature

- Miniature size with dimmer function!
- Driver free (USB Video Class) for any OS (windows XP · Vista · win7, Linux any version, MAC OS , Andriod phone)

Specification

Features:	<ul style="list-style-type: none"> • Connects to Windows XP machines USB 2.0 port • TCP Video MJPEG stream 1280 x 720 /YUV 10fps/ MJPEG 30fps 640 x 480 /30 fps 320 x 200 /30 fps • Driver free (USB Video Class) for any OS (windows XP any version, MAC OS)
Number of effective pixels	<ul style="list-style-type: none"> • 1280 x 720 /YUV 10fps/ MJPEG 30fps • 640 x 480 /30 fps • 320 x 200 /30 fps
pixel size	3 umx3 um
Image sensor	1/4" WXGA HD 720P Camera
Image area	3888 um x 2430 um
S/N Ratio	39 dB
Scan mode	progressive
Sensitivity	3300mV/(Lux)
Dark Current	20 mV/Sec
Storage temperature	-30 to 60 Degree C
Working temperature	-10 to 45 Degree C
Built-in Lens	3.4mm /F2.8
LED	white light LED x 10
Power source	DC 5V
Power current	150 mA
Dimension(mm)	Ø10 x 29.8mm

MODEL	OUTPUT
MD-VB4010L	USB 2.0 A type
MD-V4010	
MD-V4010L	
MM-V4010	Micro USB OTG B type
MM-V4010L	
MT-V4010	USB Type C
MT-V4010L	
<p>MD-VB4010L</p> <p>B: camera module</p>	



MD-V4010L



MM-V4010L