

Feature ■

- Operates in 2.4GHz frequency bands compliance of IEEE 802.11b/g/n.
- WEP,TKIP and AES,WPA,WPA2 hardware encryption schemes.
- Analog Camera Input.
- Slim WI-FI DVR.
- APP operation both on iOS / Android system.
- Can be powered by portable battery bank.
- Black/White color choice.



Model	WF-AV100
Resolution	Max D1/30fps
Video Input	NTSC / PAL Auto-Detection Standard CVBS Signal camera
Compression Algorithm	H.264 / Audio : PCM
Video File Format	AVI
Wi-Fi Standard	IEEE 802.11b/g/n 2.4GHz ISM Band
Video Recording Mode	Standard / Motion Detection
Memory Type	Supports up to 64GB SDHC Micro SD
Frame Rate	10/ 15/ 20/ 25/ 30 Adjustable
Time Stamp	YES
LED Indicator	Power / WI-FI / REC
Button Operation	Power / WI-FI / REC
Power Consumption	Max. 1.3W
Power Input	DC 5V
APP	iOS / Android
Weight	13g
Dimension	54.5x28x10 mm