

**Feature ■**

- WI-FI smart link design, Easy to setup and connect to internet.
- Operates in 2.4GHz frequency bands compliance of IEEE 802.11b/g/n.
- WEP,TKIP and AES,WPA,WPA2 hardware encryption schemes.
- Analog Camera Input.
- Wi-Fi portable external camera video camcorder.
- APP operation both on iOS / Android system.
- Built-in 1100mAh rechargeable Li-Lon battery.



Model	WF-AV200
Resolution	Max D1/30fps
Video Input	NTSC / PAL Auto-Detection Standard CVBS Signal camera
Compression Algorithm	H.264 / Audio : PCM
Video File Format	AVI
Wi-Fi Standard	IEEE 802.11b/g/n 2.4GHz ISM Band
Video Recording Mode	Standard / Motion Detection
Memory Type	Supports up to 64GB SDHC Micro SD
Frame Rate	10/ 15/ 20/ 25/ 30 Adjustable
Time Stamp	YES
LED Indicator	Power / WI-FI / REC
Power Input	DC 5V
Charge Current	500mA
Power Consumption	Max. 1.7W
Battery Type	Build-in 1100mAh Charge Circuit Li-Lon Battery
Charging Time	2.5 hours
Operating Time	Approx. 130min
APP	iOS / Android
Weight	55g
Dimension	72*36.6*16 mm