



Unit: mm

## Specification

Model	1M216711R-M5.5
Filter type	IR cut 650±10nm
Sensor type	1/4"
EFL (mm)	2.16mm
Aperture F/no	7.1
Image Circle	Ø5.07mm
Chief Ray Angle	18.02°
Field Angle (D x H x V)	149.6° : 90.6° : 66.2°
Total Track	13.35mm
Mount	M5.5 x P0.35
Diameter of lens (mm)	ø 6.5x10
TV distortion	<-39.12%

\*NO Lens holder