



Unit: mm

Specification

Model	3M4324IR-M12
Sensor type	1/2.7"
Focal Length	4.3mm±5%
F/NO	2.4±5%
Filter type	IR 650nm
BFL (mm)	5.5mm±5%(in air)
Minillum Object Distance	20cm
Lens Construction	5G
Field Angle	1/2.7"-95° ; 1/3"-80°
Mount	M12xP0.5