



Unit: mm

Specification

Model	LP0030AR-M1.2
Sensor type	1/18"
Filter type	AR
BFL (mm)	0.5mm
Aperture F/no	3.0
Depth of field	5mm~∞
Image area (D)	0.98mm
Field Angle	116°
Total Track	2.1mm
Mount	M1.2
Diameter of lens (D)	1.2mm

*NO Lens holder