



Unit: mm

Specification

Model	LP0040AR-M2.2	
Sensor type	1/13"	1/10.6"
Filter type	AR	
BFL (mm)	0.7mm	
Aperture F/no	4.0	
Depth of field	10mm~100mm	
Field Angle	90°	120°
Mount	M2.2 x P0.25	
Diameter of lens (D)	2.2mm	

*NO Lens holder