



Unit: mm

Specification

Model	LP0045AR-M1.9		
Sensor type	1/10"	1/10.6"	1/13"
Filter type	AR		
BFL (mm)	0.8mm		
Depth of field	5mm ~ 100mm		
Aperture F/no	4.5		
Field Angle	115°	95°	75°
Mount	M1.9 x P0.1		
Diameter of lens (D)	1.9mm		

*NO Lens holder