



Unit: mm

Specification

Model	LP10120IR-M
Sensor type	1/10"
Filter type	IR 645nm
BFL (mm)	1.11mm
Aperture F/no	2.8
Image Circle (mm)	1.9mm
Field Angle	69°(V) 69°(H) 120°(D)
Mount	M3.5 x P0.2
Diameter of lens (D)	3.20 ~ 3.25mm

*NO Lens holder