



Unit: mm

Specification

Model	LP1225IR-M2.6			
Sensor type	1/10"	1/10.6"	1/12"	1/18"
Field Angle (D)	150.0°	130.0°	100.0°	65.0°
Filter type	IR cut 650±10nm			
EFL (mm)	1.2mm			
Aperture F/no	2.5			
Image Circle	1.72mm			
Total Track	4.7mm			
Mount	M2.6 x P0.45			
Diameter of lens (mm)	ø 3.0			
Depth of field	10mm~100mm			

*NO Lens holder