



Unit: mm

Specification

Model	LP3434IRT-M5	LP3470IRT-M5
Sensor type	1/4"	
Field Angle (H/V/D)	61.0° x 46.4° x 77.3°	
Filter type	IR cut 650±20nm	
EFL (mm)	3.42mm	
Aperture F/no	3.81±3%	7.0
Back Focal Length	1.96mm	
Total Track	5.86mm±0.4mm	
Mount	M5.0 x P0.35	
Diameter of lens (mm)	M5x4.86	
TV distortion	<1.68%	

*NO Lens holder