



Unit: mm

## Specification

Model	LP430201R-M7
Sensor type	1/3"
Field Angle (D/H/V)	100°
Filter type	IR CUT Coating Filter T50%-650nm
EFL (mm)	4.3mm
Aperture F/no	2.0
Image Circle	ø6.3mm
Total track	10.34+0.3mm
Mount	M7x P0.0.5
Diameter of lens (mm)	M7 x 8.33
TV distortion	< -13%

\*NO Lens holder