

Feature ■

- Full HD resolution REC and HD transmission capability.
- Support FHD camera & NTSC/PAL video input.
- Encrypted video and audio data transmission.
- H.264/265 video compression.
- Bit rate auto adjust with current bandwidth.
- Two way audio & emergency push notice.
- Support 128G high capacity SD card.
- QR code scan link, setting free.
- One key operation, easy to use.
- App operation both on iOS / Android system.



accessory:



External camera resolution	Record : 1080P/720P/D1 Max. 30fps Preview : 720P/D1/CIF Max. 30fps Photo : 1080P
Video input resolution	Record/preview : D1/CIF Max Photo : D1
Compression algorithm	Video H.264 / H.265; Audio G.726
File Format	Video : AVI; Photo : JPG
Video recording mode	Standard/ motion
Model (LTE band)-optional	MP-WF200LTE-US-G(United states) : B17,B5,B4,B2 MP-WF200LTE-SA-G(South America) : B28,B5,B8,B3,B1,B7 MP-WF200LTE-EU-G(EURO) : B20,B5,B8,B3,B1,B7 MP-WF200LTE-AU(Australia) : B28,B5,B3,B1,B7(no GPS function) MP-WF200LTE-AS-G(Asia) : B20,B5,B8,B3,B1,B7 MP-WF200LTE-CA-G(china) : B20,B5,B8,B3,B1,B7,B39,B40,B41
GPS	GPS / GLONASS
Storage	Micro SD up to 128GB
OSD / Time Stamp	ID : 20 characters. Time stamp: YY-MM-DD HH:MM:SS
LED Indicator	Power / Link / REC
Vibration Alert	Power on/off ; REC on/off
Power source	DC 5V Micro USB
Power consumption	5W (Full run)
Operating temperature	-10 ~ 60 °C
Storage temperature	-40 ~ 85 °C
App	iOS / Android
Weight	60g w/o antenna.
Dimension	85 X 46.8 X 12.9 mm w/o LTE & GPS antenna