

Feature ■

- Operates in 2.4GHz frequency bands, compliance of IEEE 802.11b/g/n.
- WEP,TKIP and AES,WPA,WPA2 hardware encryption schemes.
- APP operation both on iOS / Android system.
- Build-in 2M pix Camera.
- Time stamp functionality.
- Supports up to 64G SDHC memory card.
- Vibration alert on REC and Snapshot.



Model	WF-FHD300
Resolution	1080P (Max : 25fps : Typical : 23fps)
Sensor	Build-in 2 Megapixel 1/5.8" CMOS
Lens F/No (Aperture)	F2.0
Min. Illumination	3 Lux
Angle of View	77.5°
Photo Resolution	1080P
Compression Algorithm	H.264 / Audio : PCM
Video File Format	AVI
Picture File Format	JPG
Wi-Fi Standard	IEEE 802.11b/g/n 2.4GHz ISM Band
Video Recording Mode	Standard / Motion Detection
Memory Type	Supports up to 64GB SDHC Micro SD
Frame Rate	10/ 15/ 20/ 25/ 30 Adjustable
Time Stamp	YES
LED Indicator	Charge
Vibration Alert	Power on/off ; Boot up completion REC on/off ; photo
Power Consumption	Max. 1.7W
Power Input	DC 5V / 350mA
Battery Type	Build-in 650mAh Li-Polymer Battery
Charging Time	2.5 hr
Operating Time	Approx. 90min
APP	iOS / Android
Weight	90g
Dimension	64x35x48 mm (Without PIN)