

**Feature ■**

- Operates in 2.4GHz frequency bands, compliance of IEEE 802.11b/g/n.
- WEP,TKIP and AES,WPA,WPA2 hardware encryption schemes.
- Build-in 2M pix Camera.
- Built-in 1100mAh rechargeable Li-Lon battery.
- Matchbox camera with mount for body worn surveillance.
- APP operation both on iOS / Android system



Model	WF-HD400
Resolution	480P / 720P (Max : 25fps ; Typical : 23fps)
Sensor	Build-in 2 Megapixel 1/5.8" CMOS
Lens F/No (Aperture)	F2.0
Min. Illumination	3 Lux
Angle of View	77.5°
Photo Resolution	480P / 720P
Compression Algorithm	H.264 / Audio : PCM
Video File Format	AVI
Picture File Format	JPG
Wi-Fi Standard	IEEE 802.11b/g/n 2.4GHz ISM Band
Video Recording Mode	Standard / Motion Detection
Memory Type	Supports up to 64GB SDHC Micro SD
Frame Rate	10/ 15/ 20/ 25 Adjustable
Time Stamp	YES
LED Indicator	Charge / Power / WI-FI / REC
Power Consumption	Max. 1.7W
Power Input	DC 5V
Charge Current	500mA
APP	iOS / Android
Charging Time	2.5 hours
Operating Time	Approx. 130min
Weight	53g
Dimension	72 x 36.6 x 16 mm