

Feature ■

- Establish point-to-point connectivity between devices with a two-step installation for
- Instant transmission of audio and video streaming with our Concurrent Connectivity
- Technology for operational costs
- NAT penetration with a success rate over 90%.
- High performance for 10-30% faster delivery
- Smart link server provide communication service and P2P/Relay service



Model	WF-HD500
Resolution	480P / 720P (Max 25fps Typical 23fps)
Sensor	1/4" CMOS
Lens F/No (Aperture)	F2.6
Min. Illumination	2 Lux
Angle of View	72°
Photo Resolution	480P / 720P
Compression Algorithm	H.264 / Audio : PCM
Video File Format	AVI
Picture File Format	JPG
Wi-Fi Standard	IEEE 802.11b/g/n 2.4GHz ISM Band
Video Recording Mode	Standard / Motion Detection
Memory Type	Supports up to 64GB SDHC Micro SD
Frame Rate	10/ 15/ 20/ 25 Adjustable
Time Stamp	YES
LED Indicator	Charge / Power / WI-FI / REC
Vibration Alert	YES
Power Consumption	Max. 1.7W
Power Input	DC 5V / 1000mA
Battery Type	Build-in 1450mAh Charge Circuit Li-Ion Battery
Charging Time	2hours
Operating Time	Approx. 160min
APP	iOS / Android