



## Specification

Unit: mm

Model	L13924IR-M10
Sensor type	1/3"
Field Angle	1/3.6" : 97°(V) / 130°(H) / 152.1°(D) 1/4" : 96°(V) / 119°(H) / 141°(D)
Filter type	IR
EFL (mm)	1.39mm±5%
Aperture F/no	2.4±5%
Chief Ray Angle	24.98°
Lens Construction	3 Component 4 Element
Mount	M5.5 x P0.35
TV Distortion	Under -26.8%
Back Focal Length	2.66mm±5%

\*NO Lens holder