

Model	Dimension		LED	LED size	Power input	Note
	OD	ID				
LS-02200703	2.2mm	0.7mm	white LED x 3	0402	DC 3.3V	
LS-03401704	3.4mm	1.7mm	white LED x 4	0402	DC 3.3V	
LS-03401704-940	3.4mm	1.7mm	IR 940nm LED x 4	0402	DC 3.3V	
LS-03401902	3.4mm	1.9mm	white LED x 2	0402	DC 3.3V	
LS-03602306	3.65mm	2.35mm	white LED x 6	0402	DC 3.3V	
LS-04002504	4.0mm	2.5mm	white LED x 4	0402	DC 3.3V	
LS-04002706	4.0mm	2.7mm	white LED x 6	0402	DC 3.3V	
LS-04103004	4.15mm	3.0mm	white LED x 4	0402	DC 3.3V	FPCB
LS-04202102	4.24mm	2.1mm	white LED x 2	0603	DC 3.3V	FPCB
LS-04202104	4.22mm	2.1mm	white LED x 4	0402	DC 3.3V	
LS-04202904	4.2mm	2.9mm	white LED x 4	0402	DC 3.3V	
LS-04503206	4.55mm	3.25mm	white LED x 6	0402	DC 3.3V	
LS-04803404	4.8mm	3.4mm	white LED x 4	0402	DC 3.3V	
LS-04803404-940	4.8mm	3.4mm	IR 940nm LED x 4	0402	DC 3.3V	
LS-04803406	4.8mm	3.4mm	white LED x 6	0402	DC 3.3V	
LS-04903606	4.9mm	3.6mm	white LED x 6	0402	DC 3.3V	
LS-04903606-940	4.9mm	3.6mm	IR 940nm LED x 6	0402	DC 3.3V	
LS-05203706	5.2mm	3.7mm	white LED x 6	0402	DC 3.3V	
LS-05203706-850	5.2mm	3.7mm	IR 850nm LED x 6	0402	DC 3.3V	
LS-05203706-940	5.2mm	3.7mm	IR 940nm LED x 6	0402	DC 3.3V	
LS-05404106	5.4mm	4.1mm	white LED x 6	0402	DC 3.3V	
LS-05404106-940	5.4mm	4.1mm	IR 940nm LED x 6	0402	DC 3.3V	
LS-06905108	6.9mm	5.1mm	white LED x 8	0402	DC 3.3V	
LS-07005202	7.0mm	5.2mm	white LED x 2	0402	DC 3.3V	
LS-07005410	7.0mm	5.4mm	white LED x 10	0402	DC 3.3V	
LS-07005410-850	7.0mm	5.4mm	IR 850nm LED x 10	0402	DC 3.3V	
LS-07005410-940	7.0mm	5.4mm	IR 940nm LED x 10	0402	DC 3.3V	
LS-07205206	7.2mm	5.2mm	white LED x 6	0402	DC 3.3V	
LS-07205206-850	7.3mm	5.2mm	IR 850nm LED x 6	0402	DC 3.3V	
LS-07205206-940	7.3mm	5.2mm	IR 940nm LED x 6	0402	DC 3.3V	
LS-07304008	7.3mm	4.0mm	white LED x 8	0402	DC 3.3V	
LS-07304204	7.35mm	4.2mm	white LED x 4	0402	DC 3.3V	
LS-07304206	7.35mm	4.2mm	white LED x 6	0402	DC 3.3V	
LS-07305006	7.35mm	5.0mm	white LED x 6	0402	DC 3.3V	
LS-07305208	7.3mm	5.2mm	white LED x 8	0603	DC 3.3V	
LS-07305208-850	7.35mm	5.2mm	IR 850nm LED x 8	0603	DC 3.3V	
LS-07305208-940	7.35mm	5.2mm	IR 940nm LED x 8	0603	DC 3.3V	
LS-07905104	7.9mm	5.1mm	white LED x 4	0603	DC 3.3V	
LS-08004208	8.0mm	4.2mm	white LED x 8	0603	DC 3.3V	
LS-08004210	8.0mm	4.2mm	white LED x 10	0402	DC 3.3V	
LS-08005308	8.0mm	5.3mm	white LED x 8	0402	DC 3.3V	
LS-08005310	8.0mm	5.3mm	white LED x 10	0402	DC 3.3V	
LS-08106310	8.1mm	6.3mm	white LED x 10	0402	DC 3.3V	
LS-08106310-940	8.1mm	6.3mm	IR 940nm LED x 10	0402	DC 3.3V	
LS-08805310	8.8mm	5.3mm	white LED x 10	0402	DC 3.3V	
LS-08805504	8.8mm	5.5mm	white LED x 4	0603	DC 3.3V	
LS-08805606	8.8mm	5.6mm	white LED x 6	0603	DC 3.3V	
LS-09000001-850	9.0mm		IR 850nm x 1	3535	DC 3.3V	High power
LS-09000001-940	9.0mm		IR 940nm x 1	3535	DC 3.3V	High power
LS-09005806	9.0mm	5.8mm	white LED x 6	0402	DC 3.3V	
LS-10305508	10.3mm	5.5mm	white LED x 8	0603	DC 3.3V	

continuing....

Model	Dimension		LED	LED size	Power input	Note
	OD	ID				
LS-11001E-850	11mm		IR 850nm x 1	3535	DC5~12V	high power with tube
LS-11001E-940	11mm		IR 940nm x 1	3535	DC5~12V	high power with tube
LS-11006304	11mm	6.3mm	white LED x 4	0603	DC 3.3V	
LS-11508010	11.5mm	8.0mm	white LED x 10	0402	DC 3.3V	
LS-12006304	12mm	6.3mm	white LED x 4	0603	DC 3.3V	
LS-12009512	12mm	9.5mm	white LED x 12	0603	DC 3.3V	
LS-12009512-850	12mm	9.5mm	IR 850nm LED x 12	0603	DC 3.3V	
LS-12009512-940	12mm	9.5mm	IR 940nm LED x 12	0603	DC 3.3V	
LS-13004003	13mm	4.3mm	white LED x 3	3020	DC 3.3V	
LS-13004003-850	13mm	4.3mm	IR 850nm LED x 3	3535	DC 3.3V	
LS-13004003-940	13mm	4.3mm	IR 940nm LED x 3	3535	DC 3.3V	
LS-13009503	13mm	9.5mm	white LED x 8	3014	DC 3.3V	
LS-14806804	14.9mm	7.0mm	white LED x 4	3535	DC 3.3V	
LS-14806804-850	14.9mm	7.0mm	IR 850nm LED x 4	3535	DC 3.3V	
LS-14806804-940	14.9mm	7.0mm	IR 940nm LED x 4	3535	DC 3.3V	
LS-16007008	16mm	7.0mm	white LED x 8	0603	DC 7~9V	
LS-16007008-850	16mm	7.0mm	IR 850nm LED x 8	0603	DC 7~9V	
LS-16007008-940	16mm	7.0mm	IR 940nm LED x 8	0603	DC 7~9V	
LS-23013008	23mm	13mm	white LED x 8	3020	DC 3.3V	
LS-30015016	30mm	15mm	white LED x 16	3020	DC 12V	