



Unit: mm

Specification

Model	LP11128IR-M3.5
Sensor type	1/10"
Filter type	IR 645nm
EFL (mm)	1.11mm
Aperture F/no	2.8
Image Circle (mm)	1.9mm
Field Angle	69°(V) 69°(H) 120°(D)
Mount	M3.5 x P0.2
Chiel Ray Angle	<13.0°
TV Distortion	<8%°
Composition	4 element, 3 plastic+1filter