



Unit: mm

Specification

Model	LP50035IR-M5.5	LP50070IR-M5.5
Sensor type	1/3"	
Field Angle (D/H/V)	68.4°/55.1°/41.68° (1/3")	
Filter type	IR	
EFL (mm)	5.0mm	
Aperture F/no	3.5	7.0
Minimum operating distance	400mm~∞	
Lens Construction	1C/1E+650nm IR filter	
Mount	M5.5 x P0.35	
Diameter of lens (mm)	$\phi 12 \times 13.69$	
Flange back length	4.15mm±0.3mm	

*NO Lens holder