



**Specification**

Model	200T5	20005
Image adjustable	YES	N/A
Max. frame rate	640 × 480 @ 30fps YUV 352 × 288 @ 30fps YUV 320 × 240 @ 30fps YUV 176 × 144 @ 30fps YUV 160 × 120 @ 30fps YUV	
Pixel size	2.5 um × 2.5 um	
Image sensor	1/9" Digital CMOS Camera Module	
Image area	1.6 × 1.2 mm	
Scan mode	progressive	
Sensitivity	1720 mV / lux*sec	
Dynamic range	73 dB	
UVC format	YUV	
Storage temperature	-25 to 60 Degree C	
Working temperature	0 to 50 Degree C	
Interface	USB 2.0 (Compliant with USB Video Class 1.1 standard)	
LED	N/A	
Operating system	Windows XP, Windows Vista, Window 7, Windows 8	
Power source	DC 5V	
Power current	70 mA	

**Feature**

- Miniature size
- Connector to smartphone!
- High performance.
- VGA image pixel



B200T5-73(FOV 73°)



B20005-74(FOV 74°)



B20005-120 (FOV 120°)



T20005-74 (FOV 74°)



**MD-B200T5L-120**

SERIES	CONNECTOR	CAMERA TYPE	DISPLAY	LED	LENS
M Miniature Size	D USB 2.0 Type C M Micro USB OTG Type B T USB 2.0 Type C	B Board Type VB Board Type + Dimmer V Tube Type + Dimmer	200T5 Color 200TM5 B / W 20005 Color *T Image adjustable	L White LED L8 IR 850 nm LED L9 IR 940 nm LED	73 1.33 mm / F 2.0 (73°) 73 1.33 mm / F 4.0 (73°) 74 1.32 mm / F 3.5 (74°) 120 F 4.0 (120°)

\* If the camera with LED, lens recommended for use high depth of field.