

# CCD B/W HIDDEN CAMERA

**Specifications:**

CCD B/W CAMERA	
Model No.	MS-B36XA      MS-B66XA
CCD Image Sensor	1/3 Interline CCD
Number of Effective Pixels	500X582(CCIR)
	752X582(CCIR)
	510X492(EIA)
	768X494(EIA)
Scanning System	2:1 INTERLACE
Synchronization	INTERNAL
Resolution (TV Lines)	420 TV LINE      570 TV LINE
S/N Ratio	MORE THAN 48dB
Minimum Illumination	0.02 Lux at F 1.2
Electronic Shutter	1/50 - 1/100000
Horizontal Sync Frequency	PAL 15.625kHz/NTSC 15.734kHz
Vertical Sync Frequency	PAL 50Hz/NTSC 60Hz
Gamma Consumption	0.45
Video Output	1 Vpp , 75 ohms Composite
Audio Output	Frequency 20-16000Hz,S/N ratio more than 58dB
Built-In Lens	3.6mm/F2.0
Lens Angle	3.6mm/92 Degree
Storage Temperature	-30 to 60 Degree C
Working Temperature	-10 to 45 Degree C
Power Source	DC 12V(standard)
Power Current	150mA
Dimensions	By model for deferent

**CCD B/W Hidden Camera:**

**Microphone**



**MS-BX68A**




**MS-BX62A**



**MS-BX60A**



**MS-BX61A**



**ACCESSORY: EXTENTION CABLE(sold separately)**

**Mode: LDRR20M**

**Length :20 Meter**

**Output: RCA Male For Video & Audio**

**Input: DC Plug Female For Power Input**

**Center(+),Outer(-)**

**Ordering Information:**

MODEL	LENS	MICROPHONE	NOTE
MS-B360A	3.7mm/F2.0	■	1/3 CCD M.RES.
MS-B660A	3.7mm/F2.0	■	1/3 CCD H.RES.
MS-B361A	3.7mm/F2.0	■	1/3 CCD M.RES.
MS-B661A	3.7mm/F2.0	■	1/3 CCD H.RES.
MS-B362A	3.7mm/F2.0	■	1/3 CCD M.RES.
MS-B662A	3.7mm/F2.0	■	1/3 CCD H.RES.
MS-B368A	3.7mm/F2.0	■	1/3 CCD M.RES.
MS-B668A	3.7mm/F2.0	■	1/3 CCD H.RES.

Other angle lens please inquire for details.

Note: **KS-BX6XA** (WITH 20M CABLE , ADAPTOR)

M: Medium resolution , H: High resolution