



MS-3000



MS-3000F



MS-3000M



MS-3000P



MS-3000W



MS-6000



MS-3100



MS-3100W



MS-3200



MS-3200W



MS-3600



MS-3600M


Specification

Model	Sensitivity	Frequency	S/N Ratio	Impedance	Power Input	Power Current	Output Terminal	Application
MS-3000	-48 dB	20 - 20000 Hz	More than 58 dB	600 ohms 20%(at 1K Hz)	DC 7~12V	20mA	RCA Male & Female (Optional)	Indoor (5-10 meter)
MS-6000								
MS-3100								
MS-3200								
MS-3600					DC 12V			
MS-3300	-65 dB	20 - 10000 Hz	More than 63 dB SPL	150 ohms 20%(at 1K Hz)	DC 5~12V	30mA		

Ordering Information

Model	Cable Length	Plug Type
MS-3000 MS-3100 MS-3200 MS-3300 MS-3600 MS-6000	50cm	RCA (F)
MS-3000F MS-3100F MS-3200F MS-3300F MS-3600F MS-6000F	180cm	RCA (M)
MS-3000P MS-3100P MS-3200P MS-3300P MS-3600P MS-6000P	180cm	PHONE JACK
MS-3000M MS-3100M MS-3200M MS-3300M MS-3600M MS-6000M	180cm	RCA (M)
MS-3000W MS-3100W MS-3200W MS-3300W MS-3600W MS-6000W	15cm	4 WIRE

Ultra Mini Microphone



- High resistance to mechanical shock
- Low vibration sensitivity
- Various responses available
- Lower noise than standard

MS-3300

Dimension

Model	Dimension
MS-3000	6x18x8 mm
MS-6000	∅18x8.8 mm
MS-3100	6x18x4 mm
MS-3200	
MS-3300	
MS-3600	∅12x35 mm