



Board Type



Feature

- High Performance.
- Outstanding Quality!
- Competitive Price!
- With OSD function
- HD 720P image pixel

Model	DS-HD6132
Video system	NTSC / PAL
Number of effective pixels	1312 (H) x 740(V) (NTSC & PAL)
Effective Image Area	5.51 mm x 3.10 mm (Diagonal : 6.3mm)
Pixel Size	4.20 um x 4.20 um
Image sensor	1/2.9 inch , RGB Bayer filter
S/N Ratio	39.8 [dB]
Dynamic range	55.1 [dB]
Max Frame Rate	- 30fps, 74.25MHz - 60fps, 1280x720 SMPTE296M @ 74.25MHz - 60fps, 1280x720 Bayer @ 74.25MHz
Sensitivity	7.0 [V/Lux.sec]
Horizontal sync frequency	NTSC -15.734kHz , PAL - 15.625kHz
Vertical sync frequency	NTSC - 60Hz , PAL - 50Hz
Camera consumption	0.45
Video output	1Vp-p , 75ohm composite
Storage temperature	-30 to 60 Degree C
Working temperature	-10 to 45 Degree C
Power source	Camera input: DC 12V
Power current	230mA-MAX
Dimension (mm)	32 x 32



Ordering Information

Model	Built-in Lens
DS-HD6132-3C	3.7mm/F2.0
DS-HD6132-4C	4.3mm/F2.0
DS-HD6132-3F	3.7mm/F2.0
DS-HD6132-4F	4.3mm/F2.0
DS-HD6132-3T	3.1mm/F3.4
DS-HD6132-4T	3.9mm/F3.9
DS-HD6132-3G	3.6mm/F2.0

DS-HD6132A A: W/MIC.
OSD Function : CAEMRA ID, EXPOSURE, WHITE BALANCE, DAY & NIGHT, IMAGE SETUP, FUN.SETUP.

Other information

1/3" Color Exview HAD CCD II (OSD) Camera
▶ ME-1771E

OSD Control Key