

Specification

Model	LP2839IR-M5
Sensor type	1/4"
Field Angle (D/H/V)	94.5°/74.7°/56° (1/4")
Filter type	IR CUT Coating Filter T50%-650nm
EFL (mm)	2.84mm
Aperture F/no	3.9
Image Circle	ø4.5mm
Total track	5.58mm
Mount	M5x P0.35
Back focal length	1.55mm



*NO Lens holder

Suitable Camera

Model	Image Circle	Image Sensor	Pixel Size	Resolution	Size(mm)
MO-S1555W	4.5mm	1/4" color	5.55 x 5.55um	648 x 488	6.6 x 8.5
MO-B5407	3.43mm	1/5" color	4.2 x 4.2um	640 x 480	7(D)
MO-B3506	4.5mm	1/4" color	5.55 x 5.55um	648 x 488	7.7(D)
MO-B5506	4.86mm	1/4" color	6 x 6um	648 x 488	8(D)


NOTE :



MO (Mini 4pin(male))



MQ (Waterproof 4pin(male))



MJ (Ø2.5mm phone plug)

- G : GND
- A : AUDIO
- P : DC POWER
- V : VIDEO