



Unit: mm

Specification

Model	14M32018IR-M12
Sensing area	1/3"
Focal length	3.2 mm
F/NO.	1.8
Back focal length	5.91 mm
TTL	23 mm
Field of view(D/H/V)	115°/98°/55°
Construction	6G + IR
Thread sized	M12 x P0.5