



Unit: mm

Specification

| | |
|----------------------|------------------------|
| Model | 1M80025IRC-M7 |
| Sensing area | 1/3" |
| Focal length | 8±5% |
| Back focal length | 5.8mm (in air) |
| Flange back length | 2.84mm |
| F/NO | 2.5±5% |
| Iris | Fixed |
| Field of view(D/H/V) | 45° / 36.5° / 27.5° |
| Resolution | 1.3MP |
| M.O.D | 30cm |
| Lens construction | 4 components 4 element |
| Thread sized | M7 x P0.5-6g |