



Unit: mm

Specification

Model	L3660IRS-C8M9
Coverage area	1/3"
Focal length	3.6 mm
F/NO.	6.0
Back focus length	4.04 mm
Field of view(D/H/V)	92°/73°/54° (1/2.7")
Construction	4G+IR
Thread sized	M9 x P0.5
TTL	14.33 mm