



Specification

Model	L4012IR-M12
Image circle	6 mm
Focal length	4.25 mm ± 5%
F/NO.	1.2
Back focus length	7.72 mm
Field of view(D/H/V)	80 ° / 64.2 ° / 48.3 °
Lens construction	9 Components 9 Elements
Thread sized	M12 x P0.5
TTL	34.45 mm
TV distortion	< -8.3%