



Unit: mm

### Specification

Model	LP10065-70LIR-31	LP10065-50LIR-31
Image sensor	2.4 mm	
Focal length	1.498 mm	
Back focal length	1.44 mm	
Iris	fixed	
F/NO	7.0	5.0
Field of view(D)	90° (@Image height - 1.2mm) 63° (@Image height - 0.865m)	
TV distortion	5 %	
Dimensions(mm)	$\phi 3.1 \times 1.9$	