



Unit: mm

Specification

Model	LP28339IRF-M7
Sensor area	1/3"
Focal length	2.83±5%
Flange back length	1.062mm
F/NO	3.89±5%
Track in Total	5.41mm in air
Field of view(D/H/V)	140° / 102.4° / 78.5° (1/3") 99.3° / 77.7° / 57.7° (1/4")
Resolution	VGA
Lens construction	1G+1F / 1G
Filter	IR cut-off / AR