

Specification

| | | | | |
|---------------------|--|----------------|------------|----------------|
| Dimension(mm) | | | | |
| Model | TD-B10415U | TD-B10415U-140 | TD-B10417R | TD-B10417R-140 |
| Dimension (mm) | 15 x 26.5 | 15 x 26.5 | Ø17 | Ø17 |
| Microphone | Built-in | Built-in | Built-in | Built-in |
| Built-in Lens | N / A | 5.2mm / F2.2 | N / A | 5.2mm / F2.2 |
| Pixel Size | 4.75x 4.75 µm | | | |
| Active Image Size | 9.12mm(H) X 5.13mm(V) | | | |
| Resolution | 1920x1080 @ 30fps MJPG | | | |
| Image sensor | 2/3" CMOS color | | | |
| Built-Lens | Specify when ordering | | | |
| Sensor scan mode | progressive | | | |
| Video Format | MJPG | | | |
| Sensitivity | 9900 mV/lux-sec | | | |
| Max SNR | 40.2 db | | | |
| Max Dynamic range | 74.8 db | | | |
| Storage temperature | -30 to 60 Degree C | | | |
| Working temperature | -10 to 45 Degree C | | | |
| Power source | DC 5V | | | |
| Power current | 180 mA(max) | | | |
| OS support | Windows XP, Windows Vista, Window 7, Windows 8, windows 10 | | | |

Feature

- Low light Camera
- High sensitivity!
- High performance.
- Full HD image pixel
- Camera parameter adjustable



Security surveillance Tool,
Slim size easy to be Hidden

High-Sensitivity,
Built- in microphone

Camera without LED
at 0.6 Lux enviroment !