




Specification

Dimension(mm)			
Model	TD-B55109R	RD-V55110RL-62	RD-V55110RL-2ES
Pixel Size	3.75 x 3.75 μ m		
Active Image Size	4.8mm(H) x 2.7mm(V)		
Resolution	1280 x 720 @ 30fps MJPG		
Image sensor	1/3" CMOS color		
Built-Lens	Specify when ordering		
Sensor scan mode	progressive		
Video Format	MJPG		
Sensitivity	6488 mV/lux-sec		
Max SNR	37.2 db		
Max Dynamic range	70.4 db		
Storage temperature	-30 to 60 Degree C		
Working temperature	-10 to 45 Degree C		
Power source	DC 5V		
Power current	NO LED / 130mA with LED 8pcs / 190mA		
OS support	Windows XP, Windows Vista, Window 7, Windows 8, windows 10		
Microphone	Built-in		

Model NO.

RD-V55110RL-78

① ② ③ ④ ⑤

①		②		③		④		⑤	
TD	USB 2.0 A type	B	Board type (module)	55109R	color(module)	L	white LED (8 pcs)	2ES	2.3mm/F7.0 (78°)
TM	Micro USB OTG B type	VB	Board type (module)+dimmer function	551M9R	B/W(module)	L9	IR940nm LED	62	4.4mm/F2.4 (62°)
TT	USB type-C	T	Tube type	55110R	color(tube)	L8	IR850nm LED		
RD	USB 2.0 A type	V	Tube type+dimmer function	551M10R	B/W(tube)				
RM	Micro USB OTG B type								
RT	USB type-C								
RD/ RM / RT with metal enclosure									

In **0.03 Lux** environment
Focus distance: 10cm



photo captured by RD-V55110RL-62

Feature

- Low light Camera
- High sensitivity!
- High performance and outstanding quality.
- HD 720p resolution.
- HDR Camera.