


Specification

Product Image						
Dimension(mm)						
Model	UCD-210	UCD-210M	UCD-211	UCD-211M	UCD-212-3.0	UCD-213
Dimension (mm)	86(L) x 23(W) x 12(H)	86(L) x 20.3(W) x 10(H)	99(L) x 29(W) x 15(H)	99(L) x 25(W) x 10(H)	99(L) x 29(W) x 15(H)	88.9(L) x 63(W) x 10(H)
Video input	CVBS (NTSC / PAL)	CVBS (NTSC / PAL)	CVBS (NTSC / PAL)	CVBS (NTSC / PAL)	CVBS (NTSC / PAL)	CVBS (NTSC / PAL)
UVC output	(Model: UCD-210) 640 x 480 (Model: UCD-210HN) 720 x 480 (Model: UCD-210HP) 720 x 576	(Model: UCD-210M) 640 x 480 (Model: UCD-210MHN) 720 x 480 (Model: UCD-210MHP) 720 x 576	(Model: UCD-211) 640x480;320x240@ 30fps (Model: UCD-211-N) 720x480;640x480;320x240@30fps (Model: UCD-211-P) 720x576;640x480;320x240@30fps	(Model: UCD-211M) 640x480;320x240@ 30fps (Model: UCD-211M-N) 720x480;640x480;320x240@30fps (Model: UCD-211M-P) 720x576;640x480;320x240@30fps	(Model: UCD-212-3.0) 640x480;320x240@ 30fps (Model: UCD-212-5.0-N) 720x480;640x480;320x240@30fps (Model: UCD-212-5.0-P) 720x576;640x480;320x240@30fps	(Model: UCD-213) 640x480@ 60fps (Model: UCD-213HD) 1280x720@ 60fps
UVC format output	MJPEG	MJPEG	H.264, MJPG, YUV	H.264, MJPG, YUV	H.264, MJPG, YUV	YUV
Audio	support	support	support (48kHz)	support (48kHz)	support (48kHz)	support (48kHz)
Interface	4 pin IRIS for camera USB 2.0 A type for output	4 pin IRIS for camera USB 2.0 A type for output	4 pin IRIS for camera USB 2.0 A type for output	4 pin IRIS for camera USB 2.0 A type for output	4 pin mini din for camera USB 2.0 A type for output	4 pin IRIS for camera USB 3.0 Micro-B output
Power input	DC 5V	DC 5V	DC 5V	DC 5V	DC 5V	DC 5V
Power output	DC 5V DC 3.3V (specify when ordering)	DC 5V DC 3.3V (specify when ordering)	DC 5V DC 3.3V (specify when ordering)	DC 5V DC 3.3V (specify when ordering)	DC 5V DC 3.3V (specify when ordering)	DC 5V DC 3.3V (specify when ordering)
Storage temperature	-40°C~85°C					
Working temperature	-10°C~60°C					
OS support	windows XP、Vista、windows7、windows8、windows10、MAC OS					windows8.1、windows10

Driver Free	No use to install driver to USB Video Class
Compact Size	Perfect for travel and portable use.
Plug & play	for USB video class
Upscale Image Quality (Model: UCD-213 series)	QVGA image pixel upscale to 1280 x 720(720p)
Live Video Calls	SKYPE ,YouTube and JoinNetso on
Power Output	2 power output for select (DC 5V / DC3.3V)



Model NO.

Model	Power output for camera	DVR Cover	UVC output resolution
UCD-210M-3.3V	DC 3.3V	N/A	640 x 480
UCD-210M	DC 5V	N/A	640 x 480
UCD-210-3.3V	DC 3.3V	DVR with cover	640 x 480
UCD-210	DC 5V	DVR with cover	640 x 480
UCD-211M-3.3	DC 3.3V	N/A	640 x 480
UCD-211M-3.3-N	DC 3.3V	N/A	720 x 480
UCD-211M-3.3-P	DC 3.3V	N/A	720 x 576
UCD-211-3.3	DC 3.3V	DVR with cover	640 x 480
UCD-211-3.3-N	DC 3.3V	DVR with cover	720 x 480
UCD-211-3.3-P	DC 3.3V	DVR with cover	720 x 576
UCD-211M-5.0	DC 5V	N/A	640 x 480
UCD-211M-5.0-N	DC 5V	N/A	720 x 480
UCD-211M-5.0-P	DC 5V	N/A	720 x 576
UCD-211-5.0	DC 5V	DVR with cover	640 x 480
UCD-211-5.0-N	DC 5V	DVR with cover	720 x 480
UCD-211-5.0-P	DC 5V	DVR with cover	720 x 576
UCD-212-3.3	DC 3.3V	DVR with cover	640 x 480
UCD-212-3.3-N	DC 3.3V	DVR with cover	720 x 480
UCD-212-3.3-P	DC 3.3V	DVR with cover	720 x 576
UCD-213MHD-3.3	DC 3.3V	N/A	1280 x 720
UCD-213HD-3.3	DC 3.3V	DVR with cover	1280 x 720
UCD-213M-3.3	DC 3.3V	N/A	640 x 480
UCD-213-3.3	DC 3.3V	DVR with cover	640 x 480
UCD-213MHD-5.0	DC 5V	N/A	1280 x 720
UCD-213HD-5.0	DC 5V	DVR with cover	1280 x 720
UCD-213M-5.0	DC 5V	N/A	1280 x 720
UCD-213-5.0	DC 5V	DVR with cover	1280 x 720