



Unit: mm

Specification

Model	3M37025IRV-M10	3M37025IRV-M12	3M37025ARV-M12
Sensing area	1/2.7" & 1/3" CCD/ CMOS		
Focal length	3.7 ± 5%		
F/NO.	2.5 ± 5%		
Back focal length	5.9 mm		
Field of view(D)	1/2.7" 100°, 1/3" 80°		
IRIS	Fixed		
Thread sized	M10 x P0.5	M12 x P0.5	
TTL	9 mm		
	with IR fliter		with AR fliter