



Unit: mm

### Specification

Model	3M37025WIRV-M12
Field Angle (D)	1/2.7" CCD/CMOS: 100° 1/3" CCD/CMOS: 80°
Image circle	6.0 mm
EFL	3.7 mm±5%
BFL	5.9 mm
Aperture F/no	2.5 ± 5%
TTL	9 mm
Filter type	IR
Mount	M12 x P0.5
M.O.D	30 cm

\*NO Lens holder