



Unit: mm

## Specification

Model	1M06950AR-M
Max. image circle	Ø1.748mm
Focal length	0.69
Back focal length	0.65 mm
F/NO	5.0
Working distance(WD)	5mm ≤ WD ≤ 50mm -Optimized for 15 mm
Spectral wavelength	420nm to 680nm
Field of view(D)	120°
Resolution	1MP
Chief Ray Angle at Max. IH	30.9°
Image quality	MTF@150 Lp/mm > 25%, WD = 15 mm
Distortion	33%