

Feature

- Compact size.
- Water proof IP67
- High Performance.
- Outstanding Quality!
- Competitive Price!



Specification

Model	MO-ZC54	MO-ZC524	MO-WC14
Number of effective pixels	290(NTSC) / 330k(PAL)		648x488 (NTSC/PAL)
Resolution(TV Lines)	380 TV Lines		400 TV Lines
Minimum illumination	0.6Lux		0.1Lux
Video system	NTSC / PAL		
Image sensor	1/4" CCIQ II Color Camera		
S/N Ratio	more than 50dB		
Horizontal sync frequency	NTSC(EIA) -15.734kHz , PAL(CCIR) - 15.625kHz		
Vertical sync frequency	NTSC(EIA) - 60Hz , PAL(CCIR) - 50Hz		
Camera consumption	0.45		
Video output	1Vp-p , 75ohm composite		
Storage temperature	-30 to 60 Degree C		
Working temperature	-10 to 45 Degree C		
Power source	DC 7~12 V		
Power current	80 mA-max		200 mA-max
Dimension (mm) (without bracket)	20 x 24 x29(mm)		15 x 17(mm)

INSTRUCTION (CMOS)

