

Hybrid High Resolution DVR



GU-1018

Operating System	Embedded Linux
Pentaplex Operation	Simultaneous Live, Recording, Playback, Archive and Remote Viewing
Compression Format	H.264/265,VBR/CBR
Dual Stream	YES
Internal HDD/ External HDD	8 x SATA HDD or Support 1 x eSATA
Live View	1,4,9,16
Digital Zoom	x4 Max
Recording & Playback Rate	4MP@15fps (per ch) ; other resolution@30fps (per ch)
Web interface	Live View/Live Audio/UI Control with Local interface
Playback View	1,4,9,16
Number of Channels	16CH 4MP cameras and 8CH 4MP IP cameras
Video Format	NTSC/PAL
Video out	HDMI 1920*1080/VGA 1920*1080/CVBS/16 CH Looping
PTZ Control	Admin/password Control, support 10 different Brand (up)
Recording Resolution	4MP@15fps (per ch) ; other resolution@30fps (per ch)
OSD Language	English, Japanese, Traditional Chinese, Simplified Chinese
Storage Capacity	80 TB
Audio	16 in/1 out
Alarm	16 in/1 out (Full screen display with alarm touch, for any i/o device connect)
Recording counting software	YES
Title	DVR INPUT English 32/Chinese 16 words/Numbers
RJ-45	10/1000Mbps Ethernet, TCP/IP, HTTP, PPPoE, DHCP, DDNS
Backup	USB 2.0/IE Backup

Smart Phone	Support APP Alarm message
公司資訊	
升洋資訊企業有限公司	
Web: http://www.misumi.com.tw/	
· Call: +886-2-2226-6303	
· Fax: +886-2-2222-5620	
Address: 5F-3, No.70, Jian 6th Rd., Zhonghe Dist, New Taipei City 23585, Taiwan (R.O.C.)	
地址: 新北市中和區建六路 70 號 5F-3	

