



Unit: mm

Specification

Model	L05758AR-M
F-number	AR
Sensor type	OV6946
Field of view	120°
EFL (mm)	0.57 mm
Aperture F/no	5.8
Image Circle(Max)	Ø1.04 mm
Back focal length	0.938 mm
Image quality	MTF@100lp/mm > 35%, WD=15mm
TV Distortion	-50.9%
Working distance(WD)	5mm ≤ WD ≤ 50mm optimized for 15mm

*NO Lens holder