



Specification

Model	L2525AR-00-M12
Sensor type	1/3"
Field Angle (D/H/V)	D=150°
Image circle	6.0mm
EFL	2.5mm
FBL	6.28mm ± 0.3mm
TTL	24.24mm ± 0.4mm
Aperture F/no	2.5
Mount	M12 x P0.5

*NO Lens holder